

# Eaton 16128-4XS

Catalog Number: 16128-4XS

Eaton B-Line series wall mounted panel enclosure, 16" height, 8" length, 16" width, NEMA 4X, Hinged cover, 4XS enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket



Photo is representative

## General specifications

|  |                       |
|--|-----------------------|
| <b>Product Name</b>                              | <b>Catalog Number</b> |
| Eaton B-Line series wall mounted panel enclosure | 16128-4XS             |
|  | <b>UPC</b>            |
|  | 782051406863          |
| <b>Product Length/Depth</b>                      | <b>Product Height</b> |
| 8 in   | 16 in                 |
| <b>Product Width</b>                             | <b>Product Weight</b> |
| 16 in  | 23.7 lb               |
| <b>Certifications</b>                            |                       |
| UL 50  |                       |
| CSA C22.2.                                       |                       |
| NEMA   |                       |

## defaultTaxonomyAttributeLabel

### Country of origin

US

### Special features

Stainless door clamps

### Style

Small single door

### Finish color

#4 brushed

### Color

Gray

### NEMA Rating

4X

### Cover type

Hinged

### Wall thickness

14 gauge

### Material

304 stainless steel

### Model

4XS enclosure

### Mounting method

Wall

### Closure type

Hinged

### Locking provisions

Padlock provision

### Mounting hole details

External mounting feet

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 16128-4XS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)