

# Eaton 161410-4XSQT

Catalog Number: 161410-4XSQT

Eaton B-Line series JIC panel enclosure, 16" height, 10" length, 14" width, NEMA 4X, Hinged cover, 4XSQT enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket



## General specifications

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	161410-4XSQT
UPC	Product Length/Depth
782051882162	10 in
Product Height	Product Width
16 in	14 in
Product Weight	Certifications
19.3 lb	UL 50
	CSA C22.2.
	NEMA

## Material/finish

### Material

304 stainless steel

### Wall thickness

16 gauge

### Finish color

#4 brushed

### Color

Gray

## Model

### Style

Small single door

### Model

4XSQT enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

External mounting feet

### Closure type

Hinged

### Special features

Continuous piano hinge, panel mount, 1/4 turn latches

## Standards

### NEMA Rating

4X

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 161410-4XSQT](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)