



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1614612CHC Encl 16X14X6 N12 CH Clamp CVR

Cooper B-Line/Cable Tray

| | |
|------------------|---|
| Catalog Number | 1614612CHC |
| Manufacturer | Cooper B-Line/Cable Tray |
| Description | Hinge Cover Enclosure, Steel, Type 12 Continuous Hinge, Wall Mount, Gray, Polyester Powder Coated;Phosphate Undercoat, 6 In Overall Width, 14 In Overall Length, 16 In Overall Height, 15.93 LB |
| Weight per unit | 15.9 (lbs/each) |
| Product Category | Nema Types 12 & 13 Metallic En |

Features

| | |
|------------|-------------------------------------|
| dimensions | 6.0000 IN X 14.0000 IN X 16.0000 IN |
|------------|-------------------------------------|

Material, Color, and Finish

| | |
|-------|--------------|
| Color | ANSI 61 GRAY |
|-------|--------------|

Dimensions and Weight

| | |
|------|--|
| Size | 14.00 In Width X 6.00 In Depth X 16.00 In Height |
|------|--|

Descriptions

| | |
|------------------------|---|
| Description | ENCL 16X14X6 N12 CH CLAMP CVR |
| extra long description | B-LINE 16146-12CHC TYPE 12 JIC CONT |
| Features | Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes. |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Eaton |
| GTIN | 00782051750904 |
| UPC | 782051750904 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | STEEL JUNCTION BOXES |
| Type | JIC panel enclosure |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 15.942 |

Uses, Certifications, and Standards

| | |
|-------------|-------------------------|
| Mounting | EXTERNAL FEET, WALL |
| nema rating | 12 |
| standard | UL 508A,CSA C22.2.,NEMA |