

# Eaton 16146-12CHC

Catalog Number: 16146-12CHC

Eaton B-Line series JIC panel enclosure, 16" height, 6" length, 14" width, NEMA 12, Hinged cover, 12CHC enclosure, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



## General specifications

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	16146-12CHC
UPC	Product Length/Depth
782051750904	6 in
Product Height	Product Width
16 in	14 in
Product Weight	Certifications
15.9 lb	UL 508A
	CSA C22.2.
	NEMA

## Material/finish

### Material

Carbon steel

### Wall thickness

16 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Small single door

### Model

12CHC enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

External mounting feet

### Closure type

Hinged

### Special features

Cont. piano hinge, panel mount,plated door clamps

## Standards

### NEMA Rating

12

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 16146-12CHC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)