

Eaton 16148-4QT

Catalog Number: 16148-4QT

Eaton B-Line series JIC panel enclosure, 16" height, 8" length, 14" width, NEMA 4, Hinged cover, 4QT enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



Photo is representative

General specifications

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	16148-4QT
UPC	Product Length/Depth
782051881899	8 in
Product Height	Product Width
16 in	14 in
Product Weight	Certifications
17.7 lb	UL 50
	CSA C22.2.
	NEMA

Material/finish

Material

Carbon steel

Wall thickness

16 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Small single door

Model

4QT enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Closure type

Hinged

Special features

Continuous piano hinge, panel mount, 1/4 turn latches

Standards

NEMA Rating

4

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 16148-4QT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)