

Specifications



Eaton 16204-3

Eaton Bussmann series power splicer block, 600 Vac, 600 Vdc, 175 A, Three-pole, SCCR: 200 kA, Black, Molded Thermoplastic Base, Tin-plated aluminum connector

General specifications

PRODUCT NAME	Eaton Bussmann series power splicer block
CATALOG NUMBER	16204-3
UPC	051712148658
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.414 lb
WARRANTY	Not Applicable
COMPLIANCES	Contact factory RoHS Compliant
CERTIFICATIONS	Contact Manufacturer

Electrical rating

AMPERAGE RATING	175A
SHORT-CIRCUIT RATING	SCCR: 200 kAIC
VOLTAGE RATING	600 Vac, 600 Vdc

General information

CONNECTION	Splicer
------------	---------

Physical details

COLOR	Black
MATERIAL	Molded thermoplastic base, tin plated aluminum connector
NUMBER OF POLES	Three-pole
TYPE	Power splicer block

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007 16204-3~BUSS POWER BLOCK
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2414
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 16204-3

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

