



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



16766 1/2" Hole-Hawg Drill 300/1200 RPM Kit

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 16766 |
| Manufacturer | Milwaukee Electric Tool |
| Description | Power and Torque, That'S About All That Needs to Be Said About The Hole-Hawg® Line Of Drills. The Compact Design Of This Drill Makes It Perfect For Drilling Between Studs and Joists. This Unit Will Handle Up to A 4-5/8 In. Selfeed Bit. An Extra Long Pipe Handle Helps You Control The Power. The 1676-6 Features Two Speed Ranges, 1200 and 300 RPM, This Will Greatly Increase The Versatility Of This Drill. Hi-Torque and Hi-Speed Make This The Perfect Choice For The Heavy Duty User. |
| Weight per unit | 19.2 (lbs/each) |
| Product Category | Power Tools - Corded |

Features

| | |
|-------------|---------|
| Cord Length | 8.0 |
| Switch Type | Trigger |
| Voltage | 120.0 |

Material, Color, and Finish

| | |
|------------------|-------|
| Handle Material | Metal |
| Housing Material | Metal |

Dimensions and Weight

| | |
|--------|-------|
| Height | 19.0 |
| Length | 6.0 |
| Width | 12.25 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | 1/2" HOLE-HAWG DRILL 300/1200 RPM KIT |
| extra long description | MILW 1676-6 1/2 RIGHTANGHOLEHAWG |
| Features | 1676-6 1/2 in. Hole Hawg Drill Kit |
| Long Description | Power and torque, that's about all that needs to be said about the Hole-Hawg® line of drills. The compact design of this drill makes it perfect for drilling between studs and joists. This unit will handle up to a 4-5/8 in. Selffeed bit. An extra long pipe handle helps you control the power. The 1676-6 features two speed ranges, 1200 and 300 RPM, this will greatly increase the versatility of this drill. Hi-torque and hi-speed make this the perfect choice for the heavy duty user. |
| Product Type | 1/2 Rightangholehawg |
| Short Description | 1/2 RIGHTANGHOLEHAWG |
| Special Features | Handles Up To 4-5/8 IN Selffeed Bit; Two Speed: 300 And 1200 RPM, Reversing; Powerful 7.5 AMP Motor; Powerful, Yet Compact For Large Hole Drilling Between Joists And Studs; Chuck Type: Keyed; Cord Type: 8 FT Fixed; Tool Weight: 11.500 LB; Spindle Lock: No; Metal Capacity: 1/2 IN Twist Bit; Spindle Size: 5/8-16 IN; Gear Train: Triple; Construction Type: Grounded; Length: 6-1/2 IN |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242001811 |
| Manufacturers Part Number | 1676-6 |
| UPC | 045242001811 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | POWER TOOLS |
| Type | HEAVY DUTY |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight | 11.5 |
| Weight Per each | 19.24 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Large Hole Drilling Between Joists And Studs |
|-------------|--|