



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1700CBR Vinyl Color Coding Tape 3/4"X66' (1.5 Core)

Minnesota Mining (3M)

Catalog Number	1700CBR
Manufacturer	Minnesota Mining (3M)
Description	Electrical Tape, Vinyl Material, Brown, 17 LB/In Tensile Strength, +32 °F Operating Temperature, +176 °F Operating Temperature, 66 FT Length, 3/4 In Width, 7 Mil Thickness, 0.22 LB
Weight per unit	0.2200 (lbs/each)
Product Category	Markers & Marking Tapes - Tape

Features

Dielectric Strength	1000 Volt per Mil
Voltage Rating	600 Volt

Material, Color, and Finish

Finish	Brown Safety
--------	--------------

Descriptions

Additional Information	RoHS Compliant; Breaking Strength 17 Inch-Pound
Commodity Description	TAPE
Description	VINYL COLOR CODING TAPE 3/4"X66' (1.5 CORE)

Manufacturer Information

Brand	MINNESOTA MINING (3M)
GTIN	00054007506492
Manufacturers Part Number	1700C-3/4X66FT-BR
Model	1700C
UPC	054007506492

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Jacketing, Harnessing

Packaging

Carton	10
Weight Per each	0.22

Uses, Certifications, and Standards

Approval	UL, CSA
Temperature Rating	32 TO 176 DEG F