



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1700CPR Vinyl Color Coding Tape 3/4"X66' (1.5 Core)

Minnesota Mining (3M)

Catalog Number	1700CPR
Manufacturer	Minnesota Mining (3M)
Description	Electrical Tape, Vinyl Material, Violet, 17 LB/In Tensile Strength, +32 °F Operating Temperature, +176 °F Operating Temperature, 66 FT Length, 3/4 In Width, 7 Mil Thickness, 0.21 LB
Weight per unit	0.2100 (lbs/each)
Product Category	Markers & Marking Tapes - Tape

Features

Dielectric Strength	1000 Volt per Mil
Voltage Rating	600 Volt

Material, Color, and Finish

Finish	VIOLET
--------	--------

Descriptions

Additional Information	RoHS Compliant; Breaking Strength 17 Inch-Pound
Commodity Description	TAPE
Description	VINYL COLOR CODING TAPE 3/4"X66' (1.5 CORE)

Manufacturer Information

GTIN	00051128532737
Model	1700C
UPC	051128532737

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Jacketing, Harnessing

Packaging

Carton	1
Package	10
Weight Per each	0.21

Uses, Certifications, and Standards

Approval	UL, CSA
Temperature Rating	32 TO 176 DEG F