

Eaton 1709-BOX

Catalog Number: 1709-BOX

Eaton straight blade plug , #18-10 AWG, 15A, Commercial, 125V, Back wire, Black, Brass, Thermoplastic, 5-15P, Two-pole, three-wire, grounding, Screw, Thermoplastic rubber, ED Box



General specifications

Product Name

Eaton straight blade plug

Catalog Number

1709-BOX

UPC

032664480706

Product Length/Depth

3 in

Product Height

1.5 in

Product Width

1.5 in

Product Weight

0.139 lb

Warranty

Refer to warranty document.

Compliances

RoHS Compliant

Certifications

cULus Listed

NOM

Federal Specification Classification 6221

02

UL



Powering Business Worldwide

Product specifications

Resources

Device type

Plug

Color

Black

Face/body material

Thermoplastic

Wiring method

Back wire

Material

Thermoplastic rubber

Allowable wire size

#18-10 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Rubber plug

Device grade

Commercial

NEMA configuration

5-15P

Style type

Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Voltage rating

125V

Application

Commercial

Torque rating

14 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)