

Eaton 1740

Catalog Number: 1740

Eaton Crouse-Hinds series FMC clamp type connector, FMC, 90° angle, Insulated, Malleable iron, 1-1/4"

General specifications



| | |
|--|----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series FMC clamp type connector | 1740 |
| | UPC |
| | 784564117403 |
| Product Length/Depth | Product Height |
| 3.88 in | 3.88 in |
| Product Width | Product Weight |
| 1.25 in | 1.25 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Conduit type

FMC

Style

Clamp

Material

Malleable iron

Connector type

90° angle

Insulator

Insulated

Trade size

1-1/4"

Resources

Catalogs

[Crouse-Hinds series Connectors and Couplings - FMC catalog page](#)

Certification reports

[Connectors and Couplings - FMC UL certification](#)

[Connectors and Couplings - FMC Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - 1740](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)