
## Cody Company, Inc.

## #184 Flexible Duct



## **Product Description**

Model 184 is a flexible duct with factory installed insulation and vapor barrier. Manufactured in sizes from 4" through 20" in 25 foot lengths and compactly packaged to reduce storage space and ease handling. Our flexible duct offers great versatility and substantial savings in installation time and initial cost. Available in bags or box.

## **Model 184 Flexible Duct Components**

**Internal Core (Duct) Material:** 

Polyester (Manufactured to ASTM Specifications)

**Internal Core Reinforcement:** 

High Carbon, Hard Drawn, Spring Steel Wire (Manufactured to ASTM Specifications)

**Insulation**:

Fiber Glass Wool, Continuous Blanket, Thermal Resistance (R-Value) (Test Method, ASTM C 518)

Vapor Barrier:

Metalized Polyester with Fiberglass Yarn Reinforcement

**Surface Burn Characteristics:** 

Flame Spread: 25 or less Smoke Developed: 50 or less (Test Method: UL procedure 723)

Maximum Positive Pressure: 10" Water Column Maximum Negative Pressure: 0.5" Water Column

Water Vapor Permeance 0.17 grains per sq. ft. per hour per inch of Hg. (Test Method: ASTM E 96,

Procedure A)

Troccaure Try			
Submittal Approval:			
Job:		PO No:	
Location:		Job No:	
Engineer		Representative:	
APPROVED for CONS	TRUCTION:		
Ву:	Title:	Date:	

4200 I 45, P.O. Box 1320, Ennis, TX 75120 Tel. (972) 875-5884 Fax (972) 875-0308 7951 East Evans Rd., San Antonio, TX 78266 Tel. (210) 651-5305 Fax (210) 651-5660

www.codycompany.com