

Eaton 1895V

Catalog Number: 1895V

Eaton Arrow Hart industrial grade toggle switch, Momentary toggle, #14-10 AWG, 15A, Flush, 120/277V, Back and side, Screw, Ivory, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen, 1P, Brass, Polycarbonate

General specifications



Product Name	Catalog Number
Eaton Arrow Hart industrial grade toggle switch	1895V
	UPC
	040893613499
Product Length/Depth	Product Height
1.31 in	3.28 in
Product Width	Product Weight
1 in	0.45 lb
Warranty	Certifications
Refer to warranty document.	CSA Certified
	cULus Listed
	UL Listed

Product specifications

Special features

Momentary toggle

Connector type

Screw

Switch type

Single-pole

Load type

INC

FLR

CFL

MLV

HAL

LED

ELV

Fan

Motor Control

Color

Ivory

Wiring method

Side

Material

Polycarbonate

Mounting method

Flush

Allowable wire size

#14-10 AWG

Amperage Rating

15A

Number Of Poles

Single-pole

Voltage rating

120/277 V

Terminal enclosure material

Brass

Application

Industrial

Resources

Catalogs

[Arrow Hart Buyers Guide Section E](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 1895V](#)

Torque rating

14 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)