

NEER EMT Straps

For EMT.

1901 and 1807: One Hole Click-On

Application

- Click-on type one hole straps for EMT provides support for conduit, as required by the National Electrical Code.

Material/Finish


- Steel/zinc plated

Certifications and Compliances

- UL Standard: 2239
- 1901 through 1906
UL Listed: E333806
- CSA Standard: C22.2 18.4
- 1901 through 1903
cUL Listed: E333806



1901



TH-1901 and TH-1807: Two Hole Snap-On

Application

- Snap-on type two hole straps for EMT are used where higher load bearing supports are desired.

Material/Finish


- Steel/zinc plated

Certifications and Compliances

- TH-1901 through TH-1905
UL Standard: 2239
UL Listed: E333806
CSA Standard: C22.2 18.4
cUL Listed: E333806



TH-1901



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters			
		A	B	C	D
1/2	1901	1.64/ 41.7	0.80/ 20.3	0.57/ 14.5	0.28/ 7.1
3/4	1902	1.96/ 49.8	0.98/ 24.9	0.63/ 16.0	0.28/ 7.1
1	1903	2.22/ 56.4	1.13/ 28.7	0.75/ 19.1	0.28/ 7.1
1-1/4	1904	2.86/ 72.6	1.50/ 38.1	0.87/ 22.1	0.38/ 9.7
1-1/2	1905	3.14/ 79.8	1.75/ 44.5	0.99/ 25.1	0.38/ 9.7
2	1906	3.89/ 98.8	2.00/ 50.8	1.11/ 28.2	0.44/ 11.2
2-1/2	1807	4.99/ 126.7	2.85/ 72.4	1.24/ 31.5	0.53/ 13.5
3	1808	5.55/ 141.0	3.47/ 88.1	1.25/ 31.8	0.53/ 13.5
3-1/2	1809	6.25/ 158.8	4.10/ 104.1	1.25/ 31.8	0.53/ 13.5
4	1810	7.00/ 177.8	4.51/ 114.6	1.26/ 32.0	0.53/ 13.5

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters			
		A	B	C	D
1/2	TH-1901	2.17/ 55.1	0.72/ 18.3	0.56/ 14.2	0.19/ 4.8
3/4	TH-1902	2.71/ 68.8	0.91/ 23.1	0.61/ 15.5	0.19/ 4.8
1	TH-1903	3.10/ 78.7	1.12/ 28.4	0.68/ 17.3	0.19/ 4.8
1-1/4	TH-1904	3.70/ 94.0	1.44/ 36.6	0.74/ 18.8	0.25/ 6.4
1-1/2	TH-1905	4.24/ 107.7	1.67/ 42.4	0.87/ 22.1	0.25/ 6.4
2	TH-1906	4.83/ 122.7	2.13/ 54.1	1.00/ 25.4	0.38/ 9.7
2-1/2	TH-1807	5.98/ 151.9	2.87/ 72.9	0.98/ 24.9	0.38/ 9.7
3	TH-1808	6.37/ 161.8	3.56/ 90.4	0.99/ 25.1	0.38/ 9.7
3-1/2	TH-1809	7.37/ 187.2	4.05/ 102.9	1.00/ 25.4	0.44/ 11.2
4	TH-1810	8.12/ 206.2	4.51/ 114.6	1.00/ 25.4	0.44/ 11.2