

Eaton 1MCB1200R

Catalog Number: 1MCB1200R

Eaton main circuit breaker, 1200A, Aluminum, NEMA 3R, Underground, 65 kAIC, NGS, Three-wire, Single-phase, 120/240V, (4) #4/0 AWG-500 kcmil, Gray



General specifications

Product Name

Eaton main circuit breaker

Catalog Number

1MCB1200R

UPC

786849053239

Product Length/Depth

13.8 in

Product Height

15.25 in

Product Width

20.2 in

Product Weight

135 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].

defaultTaxonomyAttributeLabel

Amperage Rating

1200 A

Bus material

Aluminum

Feed type

Bottom

Phase

Single-phase

Voltage rating

120/240 V

Utility approvals

MI : DTE Energy (Detroit Edison)

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

Enclosure

NEMA 3R

Interrupt rating

65 kAIC

Main circuit breaker

NGS

Number of wires

3

Wire size

(4) #4/0 AWG-500 kcmil

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METERING DIMENSION DWG FOR METER CTR
BREAKER MAIN 800-1200A

Specifications and datasheets

Eaton Specification Sheet - 1MCB1200R