

Eaton 1MCB1200RA

Catalog Number: 1MCB1200RA

Eaton main circuit breaker, 1200A, Aluminum, NEMA 3R, Underground, 65 kAIC, NGS, Three-wire, Single-phase, 120/240V, (4) #4/0 AWG-500 kcmil

General specifications



Photo is representative

Product Name

Eaton main circuit breaker

UPC

786689015206

Product Height

47.7 in

Product Weight

156 lb

Certifications

UL

Catalog Number

1MCB1200RA

Product Length/Depth

14.01 in

Product Width

20.17 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].

Amperage Rating

1200 A

Bus material

Aluminum

Feed type

Bottom

Phase

Single-phase

Voltage rating

120/240 V

Enclosure

NEMA 3R

Interrupt rating

65 kAIC

Main circuit breaker

NGS

Number of wires

3

Wire size

(4) #4/0 AWG-500 kcmil

Drawings[Dimensional Drawing - METERING DIMENSION DWG FOR METER CTR BREAKER MAIN 800-1200A](#)**Specifications and datasheets**[Eaton Specification Sheet - 1MCB1200RA](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)