

Eaton 1MCB1400RBCA600

Catalog Number: 1MCB1400RBCA600

Eaton main circuit breaker, 1400A, Copper, NEMA 3R, Underground, RGH, Three-wire, Single-phase, 120/240V, (6) #2 AWG-600 kcmil



General specifications

Product Name

Eaton main circuit breaker

Catalog Number

1MCB1400RBCA600

UPC

786685960050

Product Length/Depth

18.13 in

Product Height

57.13 in

Product Width

25.13 in

Product Weight

329 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].



Powering Business Worldwide

Amperage Rating

1400 A

Bus material

Copper

Feed type

Bottom

Phase

Single-phase

Voltage rating

120/240 V

Enclosure

NEMA 3R

Main circuit breaker

RGH

Number of wires

3

Wire size

(6) #2 AWG-600 kcmil

Drawings

[Dimensional Drawing - GROUP METERING MAIN BREAKER 1400A-2000A BOTTOM FEED](#)

Specifications and datasheets

[Eaton Specification Sheet - 1MCB1400RBCA600](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)