

Specifications



Photo is representative



Eaton 1MCB2000RBCA

Eaton main circuit breaker, 2000A, Copper, NEMA 3R, Underground, RGH, Three-wire, Single-phase, 120/240V, (6) #2 AWG-600 kcmil

General specifications

PRODUCT NAME	Eaton main circuit breaker
CATALOG NUMBER	1MCB2000RBCA
UPC	786685960081
PRODUCT LENGTH/DEPTH	18.13 in
PRODUCT HEIGHT	57.13 in
PRODUCT WIDTH	25.13 in
PRODUCT WEIGHT	314 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].

Product specifications

AMPERAGE RATING	2000 A
BUS MATERIAL	Copper
FEED TYPE	Bottom
PHASE	Single-phase
VOLTAGE RATING	120/240 V
ENCLOSURE	NEMA 3R
MAIN CIRCUIT BREAKER	RGH
NUMBER OF WIRES	3
WIRE SIZE	(6) #2 AWG-600 kcmil

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 1MCB2000RBCA
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

