

Eaton 1MFS1200RB

Catalog Number: 1MFS1200RB

Eaton main fusible switch, 1200A, Aluminum, NEMA 3R, Underground, Class T, Class L, 100 kAIC, Three-wire, Single-phase, 120/240V, (4) #2 AWG-600 kcmil



General specifications

Product Name

Eaton main fusible switch

Catalog Number

1MFS1200RB

UPC

782114396100

Product Length/Depth

13.94 in

Product Height

52.77 in

Product Width

33.49 in

Product Weight

220 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Class T fuse clips provided are field convertible to Class L by repositioning. No kit is needed. IMFS1200LK (3) 750 kcmil/phase (one kit/phase). IMFS1200LKN (3) 750 kcmil (neutral).

defaultTaxonomyAttributeLabel

Amperage Rating

1200A

Bus material

Aluminum

Feed type

Bottom

Fuse clip type

Class T, Class L

Phase

Single-phase

Voltage rating

120/240 V

Wire size

(4) #2 AWG-600 kcmil

Utility approvals

MI : DTE Energy (Detroit Edison)

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

Enclosure

NEMA 3R

Interrupt rating

100 kAIC

Number of wires

3

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - DIM. DWG. FOR GROUP METERED 1200A.
FUSIBLE MAIN SWITCH

Specifications and datasheets

Eaton Specification Sheet - 1MFS1200RB