

Eaton 1MM412RRLBCPS

Catalog Number: 1MM412RRLBCPS

Eaton resi meter stack, SS meter guides, Multiple metering, 125A, AI, Bus: 800A, Horn bypass, NEMA 3R, Depends on selected main circuit breaker, Four-jaw, 4, Single-phase in/single-phase out, BR2_, BRH2_, BRHH2_, Ringless, 120/240V



General specifications

Product Name	Catalog Number
Eaton residential meter stack	1MM412RRLBCPS
UPC	Product Length/Depth
786685382685	12.26 in
Product Height	Product Width
48.5 in	7.01 in
Product Weight	Warranty
66 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Special features

SS meter guides

Type

Multiple metering

Amperage Rating

125A

Bus material

Aluminum

Bus Rating

800 A

Bypass

Horn

Number of jaws

Four-jaw

Number of sockets

4

Phase

Single-phase in, single-phase out

Security

Ringless

Voltage rating

120/240 V

Utility approvals

TX : City Public Service of San Antonio (CPSB)

Enclosure

NEMA 3R

Interrupt rating

Depends on selected main circuit breaker

Secondary circuit breaker

BR2_, BRH2_, BRHH2_

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - 1MM412RRLBCPS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)