Eaton 1MP4124RRL

Catalog Number: 1MP4124RRL

Eaton meter pack, Socket amperage: 125A, Amperage rating: 125A, Aluminum, Bus rating: 400A, No bypass, Indoor/outdoor, Up to 100 KAIC, 4 Sockets, Five-jaw, Single-phase in/single-phase out, Ringless, 120/240 Vac

General specifications



Eaton meter pack

UPC

786849052492

Product Height

48.28 in

Product Weight

91 lb

Catalog Number

1MP4124RRL

Product Length/Depth

7.01 in

Product Width

24.25 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications

UL Listed



defaultTaxonomyAttributeLabel

Utility approvals

ME: Central Maine Power

GA: Georgia Power

KS: Kansas City Power and Light (KCPL) / Westar Energy

MO: Kansas City Power and Light (KCPL) / Westar Energy

TN : Middle Tennessee EMC FL : Tallahassee City Electric

IN : Indiana Michigan Power (IMP) (AEP East)
MI : Indiana Michigan Power (IMP) (AEP East)

OH: AEP Ohio (AEP East)

TN: Appalachian Power (AEP East)
VA: Appalachian Power (AEP East)
WV: Appalachian Power (AEP East)

Interrupt rating

Up to 100 KAIC

Secondary circuit breaker

BR2_, BRH2_, BRHH2_, BRX2_

Enclosure

Indoor/outdoor

Voltage rating

120/240 V

Amperage Rating

125A

Bus material

Aluminum

Bus Rating

400 A

Bypass

None

Number of jaws

Five-jaw

Number of sockets

4

Security

Ringless

Socket amperage

125A

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER PACKS, DIMENSIONS, 125A, 4 METER DEVICE

Specifications and datasheets

Eaton Specification Sheet - 1MP4124RRL



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia