

Eaton 1MP5126RRL

Catalog Number: 1MP5126RRL

Eaton meter pack, Socket amperage: 125A, Amperage rating: 125A, Aluminum, Bus rating: 600A, No bypass, Indoor/outdoor, Up to 100 KAIC, Five-jaw, 5 Sockets, Single-phase in/single-phase out, Ringless, 120/240 Vac, NEMA 3R

General specifications

Product Name	Catalog Number
Eaton meter pack	1MP5126RRL
UPC	Product Length/Depth
786849052508	41.59 in
Product Height	Product Width
36.28 in	7.01 in
Product Weight	Warranty
110 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	



defaultTaxonomyAttributeLabel

Utility approvals

ME : Central Maine Power
NC : Dominion
VA : Dominion
GA : Georgia Power
KS : Kansas City Power and Light (KCPL) / Westar Energy
MO : Kansas City Power and Light (KCPL) / Westar Energy
TN : Middle Tennessee EMC
FL : Tallahassee City Electric
IN : Indiana Michigan Power (IMP) (AEP East)
MI : Indiana Michigan Power (IMP) (AEP East)
OH : AEP Ohio (AEP East)
TN : Appalachian Power (AEP East)
VA : Appalachian Power (AEP East)
WV : Appalachian Power (AEP East)

Interrupt rating

Up to 100 KAIC

Secondary circuit breaker

BR2_, BRH2_, BRHH2_, BRX2_

Enclosure

Indoor/outdoor

Voltage rating

120/240 V

Amperage Rating

125A

Bus material

Aluminum

Bus Rating

600 A

Bypass

None

Number of jaws

Five-jaw

Number of sockets

5

Security

Ringless

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER PACKS, DIMENSIONS, 125A, 5 METER
DEVICE

Specifications and datasheets

Eaton Specification Sheet - 1MP5126RRL

Socket amperage

125A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton 1MP5126RRL

Catalog Number: 1MP5126RRL

Eaton meter pack, Socket amperage: 125A, Amperage rating: 125A, Aluminum, Bus rating: 600A, No bypass, Indoor/outdoor, Up to 100 KAIC, Five-jaw, 5 Sockets, Single-phase in/single-phase out, Ringless, 120/240 Vac, NEMA 3R

General specifications

Product Name	Catalog Number
Eaton meter pack	1MP5126RRL
UPC	Product Length/Depth
786849052508	41.59 in
Product Height	Product Width
36.28 in	7.01 in
Product Weight	Warranty
110 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	



defaultTaxonomyAttributeLabel

Utility approvals

ME : Central Maine Power
NC : Dominion
VA : Dominion
GA : Georgia Power
KS : Kansas City Power and Light (KCPL) / Westar Energy
MO : Kansas City Power and Light (KCPL) / Westar Energy
TN : Middle Tennessee EMC
FL : Tallahassee City Electric
IN : Indiana Michigan Power (IMP) (AEP East)
MI : Indiana Michigan Power (IMP) (AEP East)
OH : AEP Ohio (AEP East)
TN : Appalachian Power (AEP East)
VA : Appalachian Power (AEP East)
WV : Appalachian Power (AEP East)

Interrupt rating

Up to 100 KAIC

Secondary circuit breaker

BR2_, BRH2_, BRHH2_, BRX2_

Enclosure

Indoor/outdoor

Voltage rating

120/240 V

Amperage Rating

125A

Bus material

Aluminum

Bus Rating

600 A

Bypass

None

Number of jaws

Five-jaw

Number of sockets

5

Security

Ringless

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER PACKS, DIMENSIONS, 125A, 5 METER
DEVICE

Specifications and datasheets

Eaton Specification Sheet - 1MP5126RRL

Socket amperage

125A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia