ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

1R3006A20A120 MC 3P MR 12IN 16/1 PVC

Molex LLC

Catalog Number	1R3006A20A120
Manufacturer	Molex LLC
Description	Straight Receptacle, 13 A, 600 V Ac/DC, 3 Poles, -20 °C Operating Temperature, +105 °C Operating Temperature, #16 Awg Wire Size
Weight per unit	0.1090 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	13
connection	External Thread
orientation	Straight

Dimensions and Weight

Size	0.305m

Descriptions

Description	MC 3P MR 12IN 16/1 PVC
extra long description	MOLE 1R3006A20A120 MC 3P MR 12IN 16

Manufacturer Information

Brand	Brad
GTIN	00781725533935
sub brand	Mini-Change
UPC	781725533935

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Single Ended (pigtail)

Packaging

Carton	1
Package	12
Weight Per each	0.109

Uses, Certifications, and Standards

environmental conditions	IP67
Temperature Rating	-20 °C to +105 °C