



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2002X60 2"X60YD Masking Tape

Minnesota Mining (3M)

Catalog Number	2002X60
Manufacturer	Minnesota Mining (3M)
Description	Paper Tape, Opaque Type; Adhesive Rubber, Crepe Paper Backing Material; Tan Color; 55 Meter; 1.88 Inch; Masonry and Plaster Finish Application; 4.4 Mil Thickness; 200 Deg F Temperature Rating; Rohs Compliant; Adhesion Strength 25 Ounce Per Inch
Weight per unit	0.2000 (lbs/each)
Product Category	Markers & Marking Tapes - Tape

### Features

Length in yd	60 A
Material	CREPE PAPER
Width in mm	48 in

### Material, Color, and Finish

Color	TAN
-------	-----

### Dimensions and Weight

Length	55 Meter
Thickness	5.5 MIL
Width	48 MM

### Descriptions

Additional Information	RoHS Compliant; Adhesion Strength 25 Ounce per Inch
Commodity Description	TAPE
Description	2"X60YD MASKING TAPE
Long Description	PAPER TAPE, OPAQUE TYPE; ADHESIVE RUBBER, CREPE PAPER BACKING MATERIAL; TAN COLOR; 55 METER; 1.88 INCH; MASONRY AND PLASTER FINISH APPLICATION; 4.4 MIL THICKNESS; 200 DEG F TEMPERATURE RATING; ROHS COMPLIANT; ADHESION STRENGTH 25 OUNCE PER INCH
Product Type	Paper Tape

### Manufacturer Information

Brand	Tartan[T]
Manufacturers Part Number	200-48MM
Model	200 A

### Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Opaque



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive .....

## Packaging

Carton ..... 1 .....

Package ..... 24 .....

Weight Per each ..... 0.2 .....

## Uses, Certifications, and Standards

Application ..... MASKING, BUNDLING, HOLDING, SEALING .....

Temperature Rating ..... 200 DEG F .....














## PRODUCT REFERRAL GENERATOR

Hi Temp Insulating – 70 Tape .....	pg. 9
Terminating .....	pg. 261
Connecting .....	pg. 147

## SCOTCH TAPE 27 AND 69

FEATURES	ADVANTAGES	BENEFITS
High temperature thermosetting adhesive	Excellent solvent resistance	Improves safety
Class B rating to Class H	High temperature resistance	Provides freedom from worry
Glass cloth backing	Mechanical protection	Lasts longer and improves safety

## Specifications for Special Use Tapes

Product Name	Product Description	Tape Thickness	Temp. Rating	Typical Applications	Specs./ Certifications and Listings
 Scotch® Glass Cloth Tape 27 and 69	Woven insulating glass cloth; high temperature resistance; high mechanical strength.	27-7 mil 69-7 mil	27 is Class B temp 266°F (130°C) 69 is class H temp 356°F (180°C)	Heat-stable insulation for furnace and oven controls, motor leads, and switches.	Meets:  File E 17385 LR93411
 Scotch® Thread Sealant and Lubricant Tape 48	Pipe thread sealant that provides a leakproof seal.	3 mil	500°F (260°C)	Leakproof seal helps prevent cross threading on pipe threads.	N/A
 Scotch® Performance Masking Tape 232	Premium grade masking tape.	6.3 mil	Up to 250°F (121°C)	Paint masking tape, bundling and protecting.	N/A
 Scotch® General Purpose Masking Tape 234	General purpose masking tape.	6.0 mil	Up to 250°F (121°C)	Holding, sealing, non-critical masking.	N/A
 3M™ Paper Tape 200	Utility purpose paper tape.	4.5 mil	200°F (93°C)	Non-critical masking and holding.	N/A
 3M™ Temflex™ Cotton Friction Tape 1755	High grade friction tape. Good abrasion resistance.	15 mil	176°F (80°C)	Abrasion protection for splices and connections.	N/A
 3M™ Duct Tape 6969	Extra heavy duty duct tape; excellent adhesion, tears easily. Silver.	10.7 mil	200°F (93°C)	Moisture proofing, plumbing, duct sealing, and protecting.	Meets:  HUD and BOCA
 3M™ Duct Tape 3939	Heavy duty duct tape; good adhesion, strong backing. Silver.	9 mil	150°F (65°C)	Sealing heating ventilation and air conditioning ducts.	Meets:  HUD and BOCA
 Scotch® Heavy Duty All-Weather Duct Tape 2245	Resists harsh outdoor conditions and stays pliable.	9.5 mil	Up to 150°F (66°C)	Outdoor projects.	Meets:  HUD and BOCA

## Ordering Information for Special Use Tapes

Product Number	UPC (054007-)	Size	Inner Unit Pack	Case Qty.
<b>Scotch® Glass Cloth Electrical Tape 27 and 69</b>				
27	15066	1/2" x 66' (13 mm x 20 m)	1/box, 10/ctn	50 rolls
27	15074	3/4" x 66' (19 mm x 20 m)	1/box, 10/ctn	50 rolls
27	27477	3/4" x 60 yd. (19 mm x 54.8 m)	N/A	12 rolls
27	10570	1" x 60 yd. (25 mm x 54.8 m)	N/A	9 rolls
27	27478	1-1/2" x 60 yd. (38 mm x 54.8 m)	N/A	24 rolls
69	10083	1/2" x 66' (13 mm x 20 m)	1/box, 10/ctn	50 rolls
69	27548	1/2" x 36 yd. (13 mm x 33 m)	N/A	18 rolls
69	09910	3/4" x 66' (19 mm x 20 m)	1/box, 10/ctn	50 rolls
69	27493	3/4" x 36 yd. (19 mm x 33 m)	N/A	12 rolls
69	27494	1" x 36 yd. (25 mm x 33 m)	N/A	9 rolls
Note: Only available sizes.				
<b>Scotch® Thread Sealant and Lubricant Tape 48</b>				
48	06192	1/4" x 260" (6,3 mm x 7 m)	N/A	12 rolls
48	06195	1/2" x 260" (13 mm x 7 m)	N/A	12 rolls
48	06196	1/2" x 520" (13 mm x 13 m)	N/A	12 rolls
48	27571	1/2" x 1296" (13 mm x 33 m)	N/A	12 rolls
Note: Other widths and lengths are available.				
<b>Scotch® Performance Masking Tape 232</b>				
232	02853*	3/4" x 60 yd. (18 mm x 54.8 m)	N/A	48 rolls
232	02854*	1" x 60 yd. (24 mm x 54.8 m)	N/A	36 rolls
232	04240*	2" x 60 yd. (48 mm x 54.8 m)	N/A	24 rolls
<b>Scotch® General Purpose Masking Tape 234</b>				
234	02981*	3/4" x 60 yd. (18 mm x 54.8 m)	N/A	48 rolls
234	02982*	1" x 60 yd. (24 mm x 54.8 m)	N/A	36 rolls
234	04244*	2" x 60 yd. (48 mm x 54.8 m)	N/A	24 rolls
<b>3M™ Paper Tape 200†</b>				
200	53469††	1/2" x 60 yd. (12 mm x 54.8 m)	N/A	72 rolls
200	53464††	3/4" x 60 yd. (18 mm x 54.8 m)	N/A	48 rolls
200	53465††	1" x 60 yd. (24 mm x 54.8 m)	N/A	36 rolls
200	53470††	1-1/2" x 60 yd. (36 mm x 54.8 m)	N/A	24 rolls
200	53466††	2" x 60 yd. (48 mm x 54.8 m)	N/A	24 rolls
200	53467††	3" x 60 yd. (72 mm x 54.8 m)	N/A	12 rolls
200	53468††	4" x 60 yd. (96 mm x 54.8 m)	N/A	8 rolls
<b>3M™ Temflex™ Cotton Friction Tape 1755</b>				
1755	50218	3/4" x 60' (19 mm x 18 m)	N/A	60 rolls

\*UPC prefix 021200-

\*\*UPC prefix 051131-

\*\*\*UPC prefix 051115-

†Order product in metric units.

††UPC prefix 048011-