

Special Use Tapes

3M™ Paper Tape 200

3M™ Paper Tape 200 is a utility purpose paper tape for holding, bundling, sealing, non-critical masking and a vast number of other jobs where a pressure-sensitive tape is needed.

Adhesive Material	Rubber
Backing Material	Crepe Paper
Tape Grade	Premium
Tape Type	Special Use
Maximum Operating Temperature	200°F (93°C)
RoHS 2011/65/EU	Yes



Order No.	UPC	Color	Length	Width	Thickness	Elongation	Breaking Strength	Adhesion to Steel	Rolls per Case
200-12MM	048011-53469	Tan	55 m	12 mm	4.4 mil	8%	19 lbs/in (333 N/100 mm)	25 oz/in (27 N/100 mm)	72
200-18MM	048011-53464	Tan	55 m	18 mm	4.4 mil	8%	19 lbs/in (333 N/100 mm)	25 oz/in (27 N/100 mm)	48
200-24MM	048011-53465	Tan	55 m	24 mm	4.4 mil	8%	19 lbs/in (333 N/100 mm)	25 oz/in (27 N/100 mm)	36
200-36MM	048011-53470	Tan	55 m	36 mm	4.4 mil	8%	19 lbs/in (333 N/100 mm)	25 oz/in (27 N/100 mm)	24
200-48MM	048011-53466	Tan	55 m	48 mm	4.4 mil	8%	19 lbs/in (333 N/100 mm)	25 oz/in (27 N/100 mm)	24
200-72MM	048011-53467	Tan	55 m	72 mm	4.4 mil	8%	19 lbs/in (333 N/100 mm)	25 oz/in (27 N/100 mm)	12
200-96MM	048011-53468	Tan	55 m	96 mm	4.4 mil	8%	19 lbs/in (333 N/100 mm)	25 oz/in (27 N/100 mm)	8