



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

13405 Stemmons Frwy
75234-0000, TX Farmers Branch
Phone: 972-206-0016
Fax: 972-352-2818



2006S Copper Splice Cap Crimp Conn, 18-10 Awg, 100/Bag

Ideal

Catalog Number	2006S
Manufacturer	Ideal
Description	Splice Cap, (2) #18 Awg Conductor Size, (4) #12 Awg Conductor Size, Copper (Sleeves) Conductor Material, Crimp Terminal, 600 V Ac
Weight per unit	0.2000 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Copper Sleeves
Voltage Rating	600

Material, Color, and Finish

Finish	Zinc-Plated, Tin-Plated Steel Sleeves
--------	---------------------------------------

Descriptions

Description	COPPER SPLICE CAP CRIMP CONN, 18-10 AWG, 100/BAG
extra long description	IDEAL 2006S SPL CAP (100 BAG)
Features	Designed for making fast, permanent, pressure-type connectionsSolid copper sleeves require less crimping pressure and resistn corrosion in harsh environmentsUL 486S Listed and CSA C22.2 #188 Certified: comply with Federal Specification W-S-61D

Manufacturer Information

Brand	Buchanan
GTIN	00781789450056
UPC	781789450056

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Splice Cap

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Package	1000
Weight Per each	0.2

Uses, Certifications, and Standards

Application	For Buchanan C24 Crimp Tool And Designed For Fast, Permanent, Pressure-Type Connections
standard	CSA, UL Listed, RoHS