

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1 78626-0000, TX Georgetown Phone: 737-444-2615

Fax: 737-444-2617



standard

## 2011S Copper Splice Cap Crimp Conn, 14-4 Awg, 50/Bag

Ideal	
Catalog Number	2011\$
Manufacturer	Ideal
Description	Splice Cap, Copper Conductor Material, 600 V Ac, 0.01 LB
Weight per unit	0.0050 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts
Features	
Material	Copper Sleeves
Voltage Rating	600
Material, Color, and Finish	
Finish	Zinc-Plated, Tin-Plated Steel Sleeves
Descriptions	
Description	COPPER SPLICE CAP CRIMP CONN, 14-4 AWG, 50/BAG
extra long description	IDEAL 2011S SPL CAP, 50PC BAG
Features	Designed for making fast, permanent, pressure-type
	connectionsSolid copper sleeves require less crimping pressure
	and resistn corrosion in harsh environmentsUL 486S Listed and
	CSA C22.2 #188 Certified: comply with Federal Specification
	W-S-61D
Vlanufacturer Information	
Brand	Buchanan
GTIN	00781789450070
UPC	781789450070
Taxonomies, Classifications, and Ca	•
Category Description	Datacom Wiring Devices and Accessories
Туре	Splice Cap
Availability	
minimum qty	50
Packaging	
Carton	50
Package	500
Weight Per each	0.005
Uses, Certifications, and Standards	
Application	For Buchanan C24 Crimp Tool And Designed For Fast, Permanen
	Pressure-Type Connections

CSA, UL Listed, RoHS