ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

201575AU 475-600 3PH Monitor

Littelfuse

Catalog Number	201575AU
Manufacturer	Littelfuse
Description	The 201A-Au Is A 3-Phase, Auto-Ranging, Dual-Range Voltage Monitor That Protects 190-480VAC, 50/60HZ Motors Regardless Of Size. Has User Adjustable 1-30 Second Trip Delay, Manual or 1-500 Second Restart Delay, and 2-8% Voltage Unbalance Trip Point. The Product Also Provides A User Selectable Nominal Voltage Setpoint and The Voltage Monitor Automatically Selects Between The 200V and 400V Range. The Model 201A-Au Includes Advanced Single Led Diagnostics, Where Five Different Light Patterns Distinguish Betwee
Weight per unit	0.7000 (lbs/each)
Product Category	Monitoring Relays & Accy.

Features

Voltage Rating	475 to 600

Descriptions

Description	475-600 3PH MONITOR
extra long description	L-FSE 201-575-AU 3-PHASE PLUG-IN VO
Long Description	The 201A-AU is a 3-phase, auto-ranging, dual-range voltage monitor that protects 190-480VAC, 50/60Hz motors regardless of size. Has user adjustable 1-30 second trip delay, manual or 1-500 second restart delay, and 2-8% voltage unbalance trip point. The product also provides a user selectable nominal voltage setpoint and the voltage monitor automatically selects between the 200V and 400V range. The Model 201A-AU includes advanced single LED diagnostics, where five different light patterns distinguish betwee
Product Type	3-Phase Plug-In Volt.Monitor/5
Special Features	5YR WARR

Manufacturer Information

Brand	Littelfuse
GTIN	00079458990195
Manufacturers Part Number	201575-AU
sub brand	Symcom
UPC	079458990195

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.7

Uses, Certifications, and Standards

Operating Temperature	-40 to 158
standard	UL/CE