

# Eaton 201610-4

Catalog Number: 201610-4

Eaton B-Line series wall mounted panel enclosure, 20" height, 6" length, 16" width, NEMA 4, Hinged cover, 4 enclosure, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series wall mounted panel enclosure	201610-4
	<b>UPC</b>
	782051812206
<b>Product Length/Depth</b>	<b>Product Height</b>
6 in	20 in
<b>Product Width</b>	<b>Product Weight</b>
16 in	28.3 lb
<b>Certifications</b>	
UL 50	
CSA C22.2.	
NEMA	

## Product specifications

### Special features

Stainless door clamps

### Closure type

Hinged

### Finish color

Painted

### Color

ANSI 61 gray

### Wall thickness

16 gauge

### Material

Carbon steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

External mounting feet

### Locking provisions

Padlock provision

### NEMA Rating

4

### Model

4 enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 201610-4](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)