



#3TS 1.25 in Rigid, 1.5 in EMT Conduit Hanger

By Raco
Catalog # 2055

#3TS 1.25 in Rigid, 1.5 in EMT Conduit Hanger



*Representative Image

Features

- Furnished with nut and bolt to speed installation
- Pregalvanized finish provides corrosion protection
- Additional sizes available

Application

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls

General

Hanger Size	3
Material	Steel
UPC	050169020555

Dimensions

Dimensions	2.875 in x 0.875 in x 1.594 in
EMT Size	1.5 in
Height	1.594 in
Length	2.875 in
Rigid/IMC Size	1.25 in
Trade Size	3
Weight	0.14 lb
Width	0.875 in

Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	4800

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195968-1](#)
[Sales Drawings - HANGER WITH BOLT CUS](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2055-SPEC-EN | REV 5/2024