



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9  
78620-0000, TX Dripping Springs  
Phone: 737-317-5073  
Fax: 737-317-5074



## 2087W Radiant Dead Front Self Test GfcI 20A WH

*Pass & Seymour/Legrand*

Catalog Number	2087W
Manufacturer	Pass & Seymour/Legrand
Description	Self-Test GfcI Receptacle Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, White, 0.025 Sec Trip Time, Impact Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
indoor/outdoor	Indoor
interrupt rating	4 to 6 mA
Mounting Type	Box
Number of Gangs	1.0
Number of Wires	3
Outlet Type	Dead Front, GFCI
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	YES

### Material, Color, and Finish

Finish	SATIN
--------	-------

### Dimensions and Weight

Length	1.03
Width	1.73

### Descriptions

Description	RADIANT DEAD FRONT SELF TEST GFCI 20A WH
extra long description	P&S 2087W RADIANT DEAD FRNT SELF TE

### Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007035803
UPC	785007035803



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9  
78620-0000, TX Dripping Springs  
Phone: 737-317-5073  
Fax: 737-317-5074

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.275

## Uses, Certifications, and Standards

environmental conditions	95% Humidity, UL 94 V2
Operating Temperature	-35°C to +66°C
standard	CULUS, UL, cULus, UL Listed, FSUL