



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300  
28214-0000, NC Charlotte  
Phone: 980-249-1969  
Fax: 704-900-0948



## 2097TRLA Radiant Self Test TR Gfci 20A 125V La *Pass & Seymour/Legrand*

Catalog Number	2097TRLA
Manufacturer	Pass & Seymour/Legrand
Description	Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Light Almond, 0.025 Sec Trip Time, Tamper Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
indoor/outdoor	Indoor
interrupt rating	4 to 6 mA
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Wires	3
Outlet Type	Tamper-Resistant, GFCI
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	YES

### Material, Color, and Finish

Finish	SATIN
--------	-------

### Dimensions and Weight

Length	1.03
Width	1.73

### Descriptions

Description	RADIANT SELF TEST TR GFCI 20A 125V LA
extra long description	P&S 2097TRLA RADIANT SELF TEST TR G

### Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007036213
UPC	785007036213



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300  
28214-0000, NC Charlotte  
Phone: 980-249-1969  
Fax: 704-900-0948

## Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.275

## Uses, Certifications, and Standards

environmental conditions	95% Humidity, UL 94 V2
Operating Temperature	-35°C to +66°C
standard	UL, CULUS, cULus, UL Listed, FSUL