

# EM-M CONDUIT/PIPE TO FLANGE CLIP, SPRING STEEL, NVENT CADDY ARMOUR, 1 1/4" EMT, 1/8"-1/4" FLANGE

## CATALOG NUMBER

20M24




### **FEATURES**

Supports conduit/pipe or cable from beam flanges Snap close clip pivots a full 360° Requires only a hammer to install

### **PRODUCT ATTRIBUTES**

Material: Spring Steel
Finish: nVent CADDY Armour
EMT Conduit Size: 1 1/4"
Rigid Conduit/Pipe Size: 1 1/4"
Outer Diameter: 1.380" – 1.650"
Flange Thickness: 1/8" - 1/4"
Static Load: 75 lb

### DIAGRAMS



#### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221 Option 1 - Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

### APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

Our powerful portfolio of brands. CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER nVent.com

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.