



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street  
38501-0000, TN Cookeville  
Phone: 931-271-9933  
Fax: 931-545-4298



## 20MR16SP10C(ESX) Lamp I 20MR16/SP10/C (Esx) 12V *Sylvania-Ledvance*

Catalog Number	20MR16SP10C(ESX)
Manufacturer	Sylvania-Ledvance
Description	Tungsten Halogen Tru Aim MR16 Standard Axial Filament Uv Filter Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 20WATT 12VOLT Spot Beam
Weight per unit	0.0900 (lbs/each)
Product Category	Halogen Reflector Ar, BR, JDR,

### Features

average life	2000
Base	GU5.3 Bipin
beam angle	10
dimmable	Yes
Lamp Type	MR16
lumens	250
Shape	MR16
start type	Instant
Voltage	12.00 V
Voltage Rating	12
Wattage	20

### Material, Color, and Finish

color rendering index (cri)	100
color temperature	2800
Finish	Covered

### Descriptions

Description	LAMP I 20MR16/SP10/C (ESX) 12V
extra long description	SYL 20MR16SP10CESX-12V/54305 20MR16
Long Description	Tungsten Halogen Tru Aim MR16 STANDARD Axial Filament UV Filter Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 20Watt 12Volt Spot Beam
Product Type	20MR16SP10CESX 12V 20/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135543050
Manufacturers Part Number	20MR16/SP10/C(ESX)-12V/54305
UPC	046135543050



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street  
38501-0000, TN Cookeville  
Phone: 931-271-9933  
Fax: 931-545-4298

## Taxonomies, Classifications, and Categories

Category Description INCANDESCENT

Type HALOGEN

## Packaging

Carton 1

Package 20

Weight Per each 0.09

## Uses, Certifications, and Standards

Application Medium Screwbase or bi-pin

standard ESX