



Product Number: 58663

Order Abbreviation: 20T4Q/CL/AX 12V

General Description: Tungsten Halogen Quartz Bi-Pin STARLITE Low Pressure Clear Finish UV-Filter With Axial Filament GY6.35 Bi-Pin Base 20Watt 12Volt 4000Hr Lamp Life

Product Information

| | |
|-----------------------------------|---------------------------|
| Abbrev. With Packaging Info. | 20T4QCLAX 12V 40/CS 1/SKU |
| Approx. Lumens | 290 |
| Average Rated Life (hr) | 4000 |
| Base | GY6.35 Bipin |
| Bulb | T12 |
| Centerbeam Candlepower (cp) | 700.00 |
| Class | G (GAS) |
| Color Rendering Index (CRI) | 100 |
| Color Temperature/CCT (K) | 2800 |
| Diameter (in) | 0.472 |
| Diameter (mm) | 12.00 |
| Ecologic | YES |
| Family Brand Name | STARLITE® Bi-Pin |
| Filament | CC-8 |
| Horizontal Beam Angle (deg) | 95 |
| Lamp Finish | Clear |
| Light Center Length - LCL (in) | 24 |
| Light Center Length - LCL (mm) | 45 |
| Maximum Overall Length - MOL (mm) | 44.45 |
| Nominal Voltage (V) | 12.00 |
| Nominal Wattage (W) | 20.00 |
| Vertical Beam Angle (deg) | 999 |

Footnotes

- Starlite Low Pressure - UV Filter Quartz
- Suitable for use in unshielded fixtures. Consult most recent luminaire standards for your area to determine luminaire requirements.