



RECIPROCATING SAW BLADES

LENOX Gold™ RECIPROCATING SAW BLADES

Longest Lasting Blade. Ever.

EXTENDED BLADE LIFE

Reinforced tooth design and precision-applied titanium coating dissipate heat

FASTER CUTS

Titanium coating makes teeth more wear-resistant so they stay sharp for quicker cuts

DURABLE CONSTRUCTION

Bi-metal design stands up to the most demanding applications



LENOX T2™ TECHNOLOGY RECIPROCATING SAW BLADES

A revolutionary new blade design that delivers up to 100% longer blade life and 25% faster performance in metal cutting applications versus the prior generation of LENOX reciprocating saw blades.

	LENGTH x WIDTH x THICKNESS IN MM	5-PACK PROD NO	25-PACK PROD NO	APPLICATION	
WOOD	6 6 x 7/16 x .050 152 x 11 x 1.3	21063676GRC	21077B676GRC	Scroll cutting	
	6 6 x 3/4 x .050 152 x 19 x 1.3	21060656GR	21074B656GR		
	6 9 x 3/4 x .050 229 x 19 x 1.3	21062956GR	21076B956GR		
	6 12 x 3/4 x .050 305 x 19 x 1.3	21061156GR	21075B156GR		
METAL	10 6 x 3/4 x .035 152 x 19 x .9	21064610GR	21078B610GR		
	10 8 x 3/4 x .050 203 x 19 x 1.3	21065810GR	21079B810GR		
	14 4 x 3/4 x .035 102 x 19 x .9	21066414GR	21080B414GR		•
	14 6 x 3/4 x .035 152 x 19 x .9	21067614GR	21081B414GR		•
	18 4 x 3/4 x .035 102 x 19 x .9	21068418GR	21082B418GR		•
	18 6 x 3/4 x .035 152 x 19 x .9	21069618GR	21083B618GR		•
	18 8 x 3/4 x .035 203 x 19 x .9	21070818GR	21084B818GR		•
	24 6 x 3/4 x .035 152 x 19 x .9	21072624GR	21086B624GR		•
DEMOLITION	24 8 x 3/4 x .035 203 x 19 x .9	21073824GR	21087B824GR		•
	6 6 x 7/8 x .062 152 x 22 x 1.6	210886066GR	21220B6066GR		
	6 9 x 7/8 x .062 229 x 22 x 1.6	21090966GR	21222B966GR		
	6 12 x 7/8 x .062 305 x 22 x 1.6	21091106GR	21223B106GR		
	10 9 x 7/8 x .062 229 x 22 x 1.6	21089960GR	21221B960GR		
EXTREME METAL CUTTING	8 6 x 1 x .042 152 x 25 x 1.1	210926108GR	21224B6108GR		
	8 9 x 1 x .042 229 x 25 x 1.1	210969108GR	21228B9108GR		
	10 6 x 1 x .042 152 x 25 x 1.1	210936110GR	21225B6110GR		
	10 9 x 1 x .042 229 x 25 x 1.1	210979110GR	21229B9110GR		
	10 12 x 1 x .042 305 x 25 x 1.1	2110012110GR	21237B12110GR		
	14 6 x 1 x .042 152 x 25 x 1.1	210946114GR	21226B6114GR		•
	14 9 x 1 x .042 229 x 25 x 1.1	210989114GR	21235B9114GR		•
	14 12 x 1 x .042 305 x 25 x 1.1	2110112114GR	21238B12114GR		•
	18 6 x 1 x .042 152 x 25 x 1.1	210956118GR	21227B6118GR		•
	18 9 x 1 x .042 229 x 25 x 1.1	210999118GR	21236B9118GR		•
	18 12 x 1 x .042 305 x 25 x 1.1	2110212118GR	21239B12118GR		•