



M18™ ROCKET Dual Pack Tower Light w/One Key

Unmatched Performance, All Day Runtime. The M18™ ROCKET™ Dual Pack Tower Light w/One Key can get light to any environment on any terrain with its 3 leg position options, whether you need quick deployment, or maximum stability, or need to get the light off the ground with its 7 second setup and 5'5 deployment height. It also offers maximum portability with its stowed 22" size perfect for carrying long distances to a scene. Its rotating light head offers 5400 lumens of high output light and can run up to 26 hours with its dual battery design giving users the ability to use one or two M18 batteries. It can withstand the harshest environments with its sealed battery design making it waterproof and dustproof. The Dual Pack Tower Light is One Key capable allowing users to track and set runtimes for unmatched customization. Its high quality LEDs never need to be replaced and are backed by a limited lifetime warranty.

INCLUDES:

(1) M18™ ROCKET Dual Pack Tower Light w/One Key (2120-20)

(1) Shoulder Strap

FEATURES:

- 5400 Lumens of high quality light, Over a day of runtime
- 5'5 Extension, collapses to 22"
- Waterproof: Fully submersible up to a meter
- 5400 lumens up to 26 hours of runtime
- 7 second setup 5'5 extension
- 22" when collapsed
- Waterproof and Dustproof
- Dual Battery Design: Use one or two batteries
- 3 leg positions: stowed, Tripod, 180 degrees
- One Key capable
- 3 output modes for optimal brightness and runtime
- High mode: 5400 Lumens for up to 7 hours with (2) M18 High Demand 9.0 Batteries
- High mode: 5400 Lumens for up to 7 hours with (2) M18 High Demand 9.0 Batteries
- Medium mode: 3100 Lumens for up to 12.5 hours with (2) M18 High Demand 9.0 Batteries
- Low mode: 1600 Lumens for up to 26 hours with (2) M18 High Demand 9.0 Batteries









M18™ ROCKET Dual Pack Tower Light w/One Key

PRODUCT SPECIFICATIONS:

Length	22"
Weight	18.95 lbs
Power Source	Cordless
Width	7.1"

Battery	Compact 1.5 Ah (48-11-1815), Compact 2.0 Ah (48-11-1820), Extra Capacity 3.0 Ah (48-11-1828), Extended Capacity 4.0 Ah (48-11- 1840), Extended Capacity 5.0 Ah (48- 11-1850), Extended Capacity 6.0 Ah (48-11-1860), Extended Capacity 9.0 AH (48-11-1890)
Charger	M12/M18 multivoltage (48-59-1812), M18/M12 Radip Charger (48-59- 1808), M18/M12 Rapid Charge Station (48-59-1807, and M18 AC/DC (2710- 20)
Height	10.6"