



2-1/2 in. EMT or Rigid/IMC Set-Screw Coupling

By Raco
Catalog # 2150



*Representative Image

2-1/2 in. EMT or Rigid/IMC Set-Screw Coupling

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Conduit Type	EMT
Connector Type	Set-Screw
EU RoHS Indicator	Yes
Fitting Type	Couplings
Item Type	4D
Material	Steel
UPC	050169021507

Dimensions

Dimensions	4.094 in x 3.142 in x 3.142 in
Height	3.142 in
Length	4.094 in
Trade Size	2-1/2 in
Weight	1.431 lb
Width	3.142 in

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970 - 1](#)
[Certifications - UL COC - E195969- 1](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2150-SPEC-EN | REV 5/2024