



## 3 in. EMT or Rigid/IMC Set-Screw Coupling

By Raco  
Catalog # 2152



\*Representative Image

3 in. EMT or Rigid/IMC Set-Screw Coupling

### Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

### General

Conduit Type	EMT
Connector Type	Set-Screw
EU RoHS Indicator	Yes
Fitting Type	Couplings
Material	Steel
UPC	050169021521

### Dimensions

Dimensions	4.331 in x 3.776 in x 3.776 in
Height	3.776 in
Length	4.331 in
Trade Size	3 in
Weight	1.843 lb
Width	3.776 in

### Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	800

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195970 - 1](#)  
[Certifications - UL COC - E195969- 1](#)  
[Product Logo - Conduit](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-2152-SPEC-EN | REV 5/2024