

Products

- > [Index](#)
- > [Featured Products](#)
- > [Cross Reference](#)
- > [UPC Search](#)

Product Datasheet

[Catalog Home](#) [Home Page](#)

[Search](#)

2160 -- EMT Rigid/IMC Set Screw Connector 2-1/2" Trade Size Insulated - Steel



Product Specifications

| | |
|--------------------------------|---------------------------------------|
| Family | Rigid and IMC Fittings & EMT Fittings |
| Fittings Classification | Steel - Set Screw Connectors |
| Sub Class | Insulated |
| Trade Size | 2-1/2" |
| Standard Packaging | Carton |
| Ship Carton Length | 9.375 |
| Ship Carton Width | 7.25 |
| Ship Carton Height | 3.5 |
| WT. PER HU. | 133.5 |
| Unit Carton Quantity | 5 |
| Ship Carton Quantity | 5 |
| UPC Number | 050169021606 |
| Product UPC-A Labeled | Yes |
| Catalog PDF Page | PDF Catalog Page |

Applications

- For use in dry locations to bond EMT conduit to a box or enclosure
- RACO® steel set screw connectors provide concrete-tight connections when taped
- RACO® set screw connectors are suitable for applications above 600V

Product Features

- All steel construction insures mechanical protection for the raceway
- Tri-head screws (1/2" to 2" trade sizes) may be installed using a slotted, Philips, or Robertson head screwdriver
- 2-1/2" to 4" trade sizes are also UL listed for use on Rigid/IMC conduit, allowing for design and installation flexibility
- All components are zinc electroplated for corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation

Compliances

C / UL / US