



2-1/2 in. EMT or Rigid/IMC Set-Screw Connector, Insulated

By Raco
Catalog # 2160



*Representative Image

2-1/2 in. EMT or Rigid/IMC Set-Screw Connector, Insulated

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insulated
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.
- 2 set-screw

General

Conduit Type	EMT
Connector Type	Set-Screw
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169021606

Dimensions

Dimensions	2.875 in x 3.56 in x 3.75 in
Height	3.75 in
Length	2.875 in
Trade Size	2-1/2 in
Weight	1.402 lb
Width	3.56 in

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970 - 1](#)
[Certifications - UL COC - E195969- 1](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2160-SPEC-EN | REV 5/2024