

Products

- > [Index](#)
- > [Featured Products](#)
- > [Cross Reference](#)
- > [UPC Search](#)

Product Datasheet

[Catalog Home](#) [Home Page](#)

[Search](#)

2166 -- EMT Rigid/IMC Set Screw Connector 4" Trade Size Insulated - Steel



Product Specifications

Family	Rigid and IMC Fittings & EMT Fittings
Fittings Classification	Steel - Set Screw Connectors
Sub Class	Insulated
Trade Size	4"
Standard Packaging	Carton
Ship Carton Length	5.5
Ship Carton Width	5.5
Ship Carton Height	4.1875
WT. PER HU.	238.0
Unit Carton Quantity	1
Ship Carton Quantity	1
UPC Number	050169021668
Product UPC-A Labeled	Yes
Catalog PDF Page	PDF Catalog Page

Applications

- For use in dry locations to bond EMT conduit to a box or enclosure
- RACO® steel set screw connectors provide concrete-tight connections when taped
- RACO® set screw connectors are suitable for applications above 600V

Product Features

- All steel construction insures mechanical protection for the raceway
- Tri-head screws (1/2" to 2" trade sizes) may be installed using a slotted, Philips, or Robertson head screwdriver
- 2-1/2" to 4" trade sizes are also UL listed for use on Rigid/IMC conduit, allowing for design and installation flexibility
- All components are zinc electroplated for corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation

Compliances

C / UL / US