



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



222412 Lever-Nuts Splicing Connector, 2COND, 50/Box, Gy Wago Corporation

Catalog Number	222412
Manufacturer	Wago Corporation
Description	Splicing Connector, Aluminum;Copper Conductor Material, Non-Insulated, Gray Insulation Color, Made In Usa, 12 Awg;2.5 MM^2 Maximum Conductor Size, +85 °C Maximum Operating Temperature, 400 V Maximum Voltage Rating, 0.08 MM^2;28 Awg Minimum Conductor Size, +40 °C Minimum Operating Temperature, 0.571 In;14.5 MM Overall Length, UI International Germany GMBH;UI Underwriters Laboratories Inc Standards Met, 2-Conductor Terminal Terminal Type, 3.053 G Weight
Weight per unit	0.3365 (lbs/each)
Product Category	Splicing & Terminating Kits

Descriptions

Description	LEVER-NUTS SPLICING CONNECTOR, 2COND, 50/BOX, GY
-------------	--

Manufacturer Information

Manufacturers Part Number	222-412/K194-4045
---------------------------	-------------------

Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
----------------------	-------------

Packaging

Carton	1
Weight Per each	0.3365