

# Eaton 24208-4

Catalog Number: 24208-4

Eaton B-Line series wall mounted panel enclosure, 24" height, 8" length, 20" width, NEMA 4, Hinged cover, 4 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



## General specifications

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	24208-4
	UPC
	782051811209

Product Length/Depth	Product Height
8 in	24 in

Product Width	Product Weight
20 in	32.2 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## Product specifications

### Special features

Stainless door clamps

### Closure type

Hinged

### Finish color

Painted

### Color

ANSI 61 gray

### Wall thickness

16 gauge

### Material

Carbon steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

External mounting feet

### Locking provisions

Padlock provision

### NEMA Rating

4

### Model

4 enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 24208-4](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)