

# Eaton 242412 SCGV NK

Catalog Number: 242412 SCGV NK

Eaton B-Line series Type 1 junction boxes, 24" height, 12" length, 24" width, NEMA 1, Screw cover, SCGV NK enclosure, Surface mounted, Medium single door, No knockout, Thru holes, Galvanized steel

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series Type 1 junction boxes	242412 SCGV NK
	<b>UPC</b>
	782051002966
<b>Product Length/Depth</b>	<b>Product Height</b>
12 in	24 in
<b>Product Width</b>	<b>Product Weight</b>
24 in	43.9 lb
<b>Certifications</b>	
UL 50	
CSA C22.2.	
NEMA	



## Material/finish

### Material

Galvanized steel

### Wall thickness

14 gauge

### Finish color

Unfinished

### Color

Gray

## Model

### Style

Medium single door

### Model

SCGV NK enclosure

### Cover type

Screw

### Mounting method

Surface

### Mounting hole details

Thru holes

### Special features

Keyhole slots on cover, plated screws

## Standards

### NEMA Rating

1

### Country of origin

US

## Resources

### Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

### Specifications and datasheets

[Eaton Specification Sheet - 242412 SCGV NK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)