

Eaton 242412 SC NK

Catalog Number: 242412 SC NK

Eaton B-Line series Type 1 junction boxes, 24" height, 12" length, 24" width, NEMA 1, Screw cover, SC NK enclosure, Surface mounted, Medium single door, No knockout, Thru holes, Carbon steel



General specifications

Product Name	Catalog Number
Eaton B-Line series Type 1 junction boxes	242412 SC NK
	UPC
	782051233315

Product Length/Depth	Product Height
12 in	24 in

Product Width	Product Weight
24 in	43.9 lb

Certifications

UL 50
CSA C22.2.
NEMA

Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

SC NK enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

Thru holes

Special features

Keyhole slots on cover, plated screws

Standards

NEMA Rating

1

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 242412 SC NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)