

Eaton 24246 SCG

Catalog Number: 24246 SCG

Eaton B-Line series Type 3/3R junction boxes, 24" height, 6" length, 24" width, NEMA 3 and 12, Screw cover, SCG enclosure, Surface mounted, Medium single door, No mounting provisions, Galvanized steel, Oil-resistant gasket, gasketed screws



General specifications

Product Name	Catalog Number
Eaton B-Line series Type 3/3R junction boxes	24246 SCG
	UPC
	782051108781
Product Length/Depth	Product Height
6 in	24 in
Product Width	Product Weight
24 in	48.6 lb

Certifications

UL 50
CSA C22.2.
NEMA

Material/finish

Material

Galvanized steel

Wall thickness

14 gauge

Finish color

Unfinished

Color

Gray

Model

Style

Medium single door

Model

SCG enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

No mounting provisions

Standards

NEMA Rating

3

12

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 24246 SCG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)