

Eaton 24246 SCGV NK

Catalog Number: 24246 SCGV NK

Eaton B-Line series Type 1 junction boxes, 24" height, 6" length, 24" width, NEMA 1, Screw cover, SCGV NK enclosure, Surface mounted, Medium single door, No knockout, Thru holes, Galvanized steel



General specifications

Product Name	Catalog Number
Eaton B-Line series Type 1 junction boxes	24246 SCGV NK
	UPC
	782051002676

Product Length/Depth	Product Height
6 in	24 in

Product Width	Product Weight
24 in	34.2 lb

Certifications

UL 50
CSA C22.2.
NEMA

Material/finish

Material

Galvanized steel

Wall thickness

14 gauge

Finish color

Unfinished

Color

Gray

Model

Style

Medium single door

Model

SCGV NK enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

Thru holes

Special features

Keyhole slots on cover, plated screws

Standards

NEMA Rating

1

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 24246 SCGV NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)