

Eaton 24248 RTSC

Catalog Number: 24248 RTSC

Eaton B-Line series Type 3/3R junction boxes, 24" height, 8" length, 24" width, NEMA 3R, Screw cover, RTSC enclosure, Surface mounted, Medium single door, 9 bottom knockouts, Embossed thru holes, Carbon steel

General specifications



Product Name	Catalog Number
Eaton B-Line series Type 3/3R junction boxes	24248 RTSC
	UPC
	782051348002

Product Length/Depth	Product Height
8 in	24 in

Product Width	Product Weight
24 in	44.5 lb

Certifications

UL 50
CSA C22.2.
NEMA

Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

RTSC enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

Embossed thru holes

Closure type

Flanged cover

Special features

Rain hood, plated screws

Bottom knockouts

9

Standards

NEMA Rating

3R

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 24248 RTSC](#)