


Screw Cover Type 1 Junction and Pull Boxes



Application

- Designed for use as junction and pull boxes

Construction

- Formed from code gauge, low carbon steel
- Concentric knockouts four sides in box sizes noted*
- Keyhole slotted cover allows plated screws to stay in place
- Complies with UL 50
- Complies with CSA Type 1, specify CSA label when ordering
- Powder coated available without knockouts - to order use SCNK

Finish

- Grey polyester powder thermoset over phosphatized surface
- Optional powder coat colors available
- Mill galvanized available - to order use SCG, standard without knockouts

Specials

- Custom sizes and modifications available

Popular sizes in stock

When ordering always specify width, height and depth

Add 5% to quantities ordered less than standard cartons



Catalog #	NAED#	Size W"xH"xD"	STD CTN	Weight	User Price
*444SC	1515 22010	4x4x4	6	1	6.88
*464SC	1515 22030	4x6x4	4	2	7.55
*664SC	1515 22130	6x6x4	12	3	7.77
*684SC	1515 22160	6x8x4	8	3	9.44
*6124SC	1515 22166	6x12x4	2	5	13.33
*884SC	1515 22280	8x8x4	12	4	11.11
*8104SC	1515 22320	8x10x4	6	5	12.77
*8124SC	1515 22360	8x12x4	4	6	14.44
*10104SC	1515 22430	10x10x4	6	6	14.44
*10124SC	1515 22480	10x12x4	2	7	16.66
*12124SC	1515 22580	12x12x4	6	8	18.33
*12164SC	1515 22660	12x16x4	2	10	26.66
*12184SC	1515 22700	12x18x4	2	11	28.88
16164SC	1515 22940	16x16x4	1	12	32.77
18184SC	1515 23020	18x18x4	2	16	37.77
18244SC	1515 23090	18x24x4	1	21	71.11
24244SC	1515 23290	24x24x4	1	27	88.88
*666SC	1515 22140	6x6x6	6	3	10.00
*686SC	1515 22170	6x8x6	6	4	12.77
*6126SC	1515 22180	6x12x6	4	6	17.73
*886SC	1515 22290	8x8x6	4	5	14.66
*8106SC	1515 22330	8x10x6	4	6	15.55
*8126SC	1515 22370	8x12x6	2	7	19.44
*10106SC	1515 22440	10x10x6	4	7	19.44
*10126SC	1515 22490	10x12x6	2	8	21.11
*12126SC	1515 22590	12x12x6	4	10	23.33
*12166SC	1515 22670	12x16x6	1	12	32.22
*12186SC	1515 22710	12x18x6	2	14	32.22
*12246SC	1515 22760	12x24x6	1	17	45.55
16186SC	1515 22900	16x18x6	1	16	43.33
16166SC	1515 22950	16x16x6	1	14	34.66
18186SC	1515 23030	18x18x6	2	19	42.22
18246SC	1515 23100	18x24x6	2	24	77.77
24246SC	1515 23300	24x24x6	2	30	93.33


*with knockouts

Catalog #	NAED#	Size W"xH"xD"	STD CTN	Weight	User Price
30306SC	1515 23420	30x30x6	1	50	166.66
30366SC	1515 23430	30x36x6	1	55	200.00
36366SC	1515 23440	36x36x6	1	60	222.22
888SC	1515 22300	8x8x8	2	6	18.88
12128SC	1515 22600	12x12x8	2	11	31.11
12188SC	1515 22720	12x18x8	1	20	44.44
18188SC	1515 23040	18x18x8	2	20	55.55
18248SC	1515 23110	18x24x8	1	27	87.77
24248SC	1515 23310	24x24x8	1	34	106.66
24308SC	1515 23460	24x30x8	1	44	133.33
24368SC	1515 23470	24x36x8	1	51	157.77
30308SC	1515 23480	30x30x8	1	51	177.77
30368SC	1515 23490	30x36x8	1	61	222.22
36368SC	1515 23500	36x36x8	1	78	255.55
121210SC	1515 22610	12x12x10	1	13	35.55
121810SC	1515 22611	12x18x10	1	18	46.66
181810SC	1515 23050	18x18x10	1	23	62.22
182410SC	1515 23119	18x24x10	1	30	100.00
242410SC	1515 23320	24x24x10	1	38	124.44
243010SC	1515 23510	24x30x10	1	46	160.00
243610SC	1515 23520	24x36x10	1	55	204.44
303010SC	1515 23530	30x30x10	1	60	208.88
303610SC	1515 23540	30x36x10	1	70	231.11
363610SC	1515 23550	36x36x10	1	80	260.00
121212SC	1515 22620	12x12x12	1	15	42.22
181812SC	1515 23060	18x18x12	1	25	73.33
182412SC	1515 23120	18x24x12	1	35	111.11
242412SC	1515 23330	24x24x12	1	44	133.33
243012SC	1515 23560	24x30x12	1	51	173.33
243612SC	1515 23570	24x36x12	1	65	214.00
303012SC	1515 23580	30x30x12	1	65	233.00
303612SC	1515 23590	30x36x12	1	80	244.44
363612SC	1515 23600	36x36x12	1	87	277.77

Prices subject to change without notice



P.O. Box 462321, GARLAND, TEXAS 75046
 (972) 272-9502 1-800-657-6100
 TOLL FREE FAX 1-800-677-JBOX(5269)



Powder Coated *CUSTOM* Enclosures

Design assistance, custom tooling, rapid response. National distribution, environmentally responsible. Currently serving the following industries:

- Irrigation System
- Energy Management
- Security and Fire Alarm
- Pool and Spa
- Tree Lighting
- Outdoor Advertising
- Transformer Enclosures
- Pollution Control
- Motor Controls
- Elevator
- Government Jobs
CAGE #0HTC9

P.O. Box 462321, GARLAND, TEXAS 75046
(972) 272-9502 1-800-657-6100
TOLL FREE FAX 1-800-677-JBOX(5269)

Unity
MANUFACTURING

GENERAL CONDITIONS OF SALE

UNITY ENCLOSURES are sold through wholesale distributors nationwide.

TERMS: Two percent (2%) 10th prox net 30 days. All orders shipped by the 25th of the month are payable on the 10th of the following month.

MINIMUM BILLING: One hundred dollars (\$100.00) Net plus transportation charge.

ERRORS: All clerical errors subject to correction.

FREIGHT: Liberal freight terms, consult factory. There will be a \$25.00 charge for bus station or post office delivery. There will be a \$5.00 handling charge for all prepay and charge shipments.

LOSS OR DAMAGE IN TRANSIT: Our responsibility ceases with delivery to the carrier, at which time title passes to the purchaser and all claims for loss, damage or delay must be made to the carrier by the purchaser.

SHIPPING SCHEDULES: Published lead times and estimated shipping dates are only approximate based on the normal uninterrupted flow of production activity and are in no way guaranteed.

RETURN POLICY: No goods may be returned without first obtaining our express written permission. Goods that arrive without permission will be refused and returned to the shipper. Only standard catalog items will be considered for return. Items must be of current design and in resalable condition, which were shipped not more than one year prior to date of return request. Return shipment must be on a prepaid freight basis. Only a credit memo can be issued for return goods and this memo will be subject to a deduction for outgoing freight similar to that of the return cost, a 20% restocking charge and the cost of any rework required.

CANCELLATION: An order once placed with us and accepted by us can be cancelled only with our express written consent and upon terms that will indemnify the company. Orders for SPECIALS, or standard goods in quantities larger than normal inventory, may NOT be cancelled once order is placed in production.

SPECIALS: Unity Manufacturing welcomes the opportunity to quote on your special enclosure needs. Many custom features can be provided. Purchase orders received for non-catalog items are not cancelable and after shipment may not be returned.

WARRANTY: Unity Manufacturing warrants that its products shall be free from defects in material for a period of one year from date of shipment from its plant. If after our inspection a defect is revealed, Unity Manufacturing will not be held responsible for (1) any amount beyond the price of the product, (2) any unauthorized repair. This warranty shall not apply to any product that shows evidence of neglect, misuse or misinstallation, or that has been repaired or altered by any party other than this company. This warranty is and shall be in lieu of all other warranties, expressed or implied.

All products manufactured in the U.S.A.

Commercial And Government Entity (CAGE) Code 0HTC9

NEMA ENCLOSURE TYPES

NEMA TYPE 1: General purpose indoor - intended primarily to prevent accidental contact with enclosed equipment, in areas where unusual service conditions do not exist.

NEMA TYPE 3R: Rainproof and sleet resistant - outdoor- intended to protect enclosed equipment against rain.

NEMA TYPE 3: Dust tight, rain tight, sleet resistant - outdoor - intended to protect enclosed equipment against wind, dust and water.

Members of:

National Association of Manufacturers
NEMRA
Dallas Hispanic Chamber of Commerce
Precision Metalforming Association

Defense Manufacturing & Supplies Assoc.
NAED
I.A.E.I.

unity
MANUFACTURING

P.O. Box 462321, GARLAND, TEXAS 75046
(972) 272-9502 1-800-657-6100
TOLL FREE FAX 1-800-677-JBOX(5269)